

## Branch Circuit Breakers Pow-R-Line 1a, CBL, CBM 240 Vac Maximum:

For use on 1 and 3 phase (2, 3 and 4 wire) systems -  
240 Vac maximum

### Standard (1" per pole) breakers - 10kA

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
10kA	10	BAB1010	N / A	N / A
10kA	15	BAB1015 <sup>①</sup>	BAB2015	BAB3015H
10kA	20	BAB1020 <sup>①</sup>	BAB2020	BAB3020H
10kA	25	BAB1025	BAB2025	BAB3025H
10kA	30	BAB1030	BAB2030	BAB3030H
10kA	40	BAB1040	BAB2040	BAB3040H
10kA	50	BAB1050	BAB2050	BAB3050H
10kA	60	BAB1060	BAB2060	BAB3060H
10kA	70	BAB1070	BAB2070	BAB3070H
10kA	90	N / A	BAB2090	BAB3090H
10kA	100	BAB1100	BAB2100	BAB3100H
10kA	125	N / A	BAB2125	N / A

### Duplex (twin singles in 1") breakers - 10kA

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
10kA	15/15	DNBA1515	N / A	N / A
10kA	20/20	DNBA2020	N / A	N / A
10kA	30/30	DNBA3030	N / A	N / A

### Ground Fault breakers (5mA. people protectors) -10kA

NOTE: GFCBB replaced with QBGF Dec. 1st, 2003

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
10kA	15	QBGF1015	QBGF2015	N / A
10kA	20	QBGF1020	QBGF2020	N / A
10kA	30	QBGF1030	QBGF2030	N / A
10kA	40	QBGF1040	QBGF2040	N / A
10kA	50	N/A	QBGF2050	N/A

### High I.C. Ground Fault breakers (5mA. people protectors) - 22kA

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
22kA	15	QBHGF1015	QBHGF2015	N / A
22kA	20	QBHGF1020	QBHGF2020	N / A
22kA	30	QBHGF1030	QBHGF2030	N / A

<sup>①</sup> Switching duty rated for 120Vac fluorescent light applications.

### High I.C. (1" per pole) breakers - 22kA

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
22kA	15	QBHW1015 <sup>①</sup>	QBHW2015	QBHW3015H
22kA	20	QBHW1020 <sup>①</sup>	QBHW2020	QBHW3020H
22kA	30	QBHW1030	QBHW2030	QBHW3030H
22kA	40	QBHW1040	QBHW2040	QBHW3040H
22kA	50	QBHW1050	QBHW2050	QBHW3050H
22kA	60	QBHW1060	QBHW2060	QBHW3060H
22kA	70	QBHW1070	QBHW2070	QBHW3070H
22kA	90	N / A	QBHW2090	QBHW3090H
22kA	100	N / A	QBHW2100	QBHW3100H
22kA	125	N/A	QBHW2125	N/A

### Very High I.C. (1" per pole) breakers - 65kA (Replaces old HBA breaker)

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
42kA	15	HBAW1015	HBAW2015	HBAW3015H
42kA	20	HBAW1020	HBAW2020	HBAW3020H
42kA	30	HBAW1030	HBAW2030	N / A

### High Intensity Discharge (HID) rated breakers - 10kA

I.C Value	Amperes. Rating	1 Pole Catalogue No.	2 Pole Catalogue No.	3 Pole Cat / Style
10kA	15	BAB1015D	N / A	N / A
10kA	20	BAB1020D	N / A	N / A

### Accessories

Catalogue No.	Description
BRKSCREW	Mounting Screw for PRL1a/2a Branch Breakers (PKG 100)
BRDL1-10	Padlock Device -QBGF 1/2 pole (pkg of 10)
QL23NPL	Heavy Duty Lockdog - 2 / 3 pole BAB / QBHW / HBA
QL1NPL	Heavy Duty Lockdog - 1 pole BAB / QBHW / HBA
QL123PL	Padlock Device - 1, 2, 3, pole BAB / QBHW / HBA
QL1PL	Padlock Device - 1 pole BAB / QBHW / HBA (pkg of 10)
PL12NAK42	42 cct neutral adder kit - use with all DNBA breakers (M43)**

\*\*Use the neutral adder kit to ensure enough neutral connection points when using more than 50% fill of DNBA breakers.