
NUWATT®





Surface Mount / Flush Mount LED Flat Panels


Applications:


- 2 Sizes- 1' x 1', 1' x 2'
- Flush Mount, Surface Mount or Drop Ceiling
- Use in your- Entryway, Kitchen, Bathroom, Living Room, Hallway & Bar

Product Information:

- Internal flicker-free triac-dimmable driver
- 5CCT Kelvin Selectable Switch
- Compatible with Most Triac Wall Dimmers On the Market
- Only 1" Thick in Size

ENERGY STAR DLC c UL us LISTED






Aluminum Trim



CCT Switch




Slide Bracket Lock






Included Hardware



Mounting Bracket

- 5 Kelvin Selectable
- 22 Watt
- 2000 Lumens
- Triac Dimmable
- Integrated LED
- IP20 Rated
- 120V

RETAIL READY STAND OUT PACKAGING



Packaging subject to size change based on product size







1" X 1" SURFACE MOUNT PANEL

☐ NW-SM-1X1-5CT-18W-WH

LUMENS	1,500
WATTAGE	18W
VOLTAGE	120V
TRIM	WH- White
COLOR TEMP	27/30/35/40/50K
BEAM ANGLE	120˚
LIFE HOURS	50,000
CRI	80
DIMMABLE	Yes

1" X 2" SURFACE MOUNT PANEL

☐ NW-SM-1X2-5CT-22W-WH

LUMENS	2,000
WATTAGE	22W
VOLTAGE	120V
TRIM	WH- White
COLOR TEMP	27/30/35/40/50K
BEAM ANGLE	120˚
LIFE HOURS	50,000
CRI	80
DIMMABLE	Yes