



SWC008PNR



33.88" x 5.88" x 22.13" (H x W x D)

6" wide built-in undercounter wine cellar with panel-ready glass door

Highlights:

Unique 6 inch width lets you transform the smallest space into convenient wine storage and display

Panel-ready door trim lets you transform the look to match your own design

Front-breathing design for built-in installation

Product Features:

6" Wide Built-In Wine Cellar	Single zone wine cellar sized for built-in installation in 6" wide spaces
Customizable look	Panel-ready door lets you customize the unit for a seamless look that integrates into your kitchen
Easy panel installation with included 2-piece bracket kit	Enhanced panel execution allows the unit to be flush with cabinets (recommended panel size: 3/4" thickness at 30" H x 5 3/4 W with a 3 1/4" inner frame)
Flexible style	Innovative panel-ready bracket kit allows easy custom panel installation, but can also be removed cleanly if you redesign your space and prefer the look of a stainless steel trimmed door
Fully articulating hinge	European style hinge design ensures a flush fit and allows for a smoother opening
Seamless stainless steel door trim	Single-piece stainless steel door trim frames the window for a premium look
Slim 6 inch width	Uniquely slim fit lets you transform extra cabinet space into a 7-bottle wine storage center
Designed for built-in use	Make the best use of space by installing your appliance under the counter
Commercial grade design	Meets UL-471 commercial standards



SWC008PNR Specifications:

Overview	
Nominal Height	34.0" (86 cm)
Height of Cabinet	33.88" (86 cm)
Nominal Width	6.0" (15 cm)
Width	5.88" (15 cm)
Nominal Depth	22.13" (56 cm)
Depth	22.13" (56 cm)
Depth with Panel	22.88" (58 cm)
Depth with door at 90°	28.63" (73 cm)
Bottles	7 bottles
Defrost Type	Automatic
Door	Glass/Panel-Ready Frame
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	44.0 lbs. (20 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101159812
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Yes
Thermostat Type	Digital
Interior Light	Yes
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	0.57 oz.
High Side PSI	270.0
Low Side PSI	105.0
Interior Height 1	25.88" (66 cm)
Interior Width 1	3.5" (9 cm)
Interior Depth 1	14.25" (36 cm)
Compressor Step Height	3.0" (8 cm)

Compressor Step Width	3.5" (9 cm)
Compressor Step Depth	6.0" (15 cm)
Temperature Range	41 to 72°F
Sabbath Mode	Yes
Sound Level	33.8 dB

