



Project / Job Name:

Location:

Fixture Type:

Notes:

S14401 - 20/14/6.5 Watt LED A21 Three-Way Lamp; 27K/3K/35K/4K/5K CCT; Lumens Selectable; Medium Double Contact Base; Plastic; 120 Volt; 1-Pack



GENERAL

Company	SATCO
EA Height	5.44
EA Width	2.8
EA Length	2.8
Material	Plastic
Fixture Type	3-Way
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<150%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Additional Info	Default Wattage: 20W; Three Way Lamp
Amps	0.205A
IOT Enabled	No
Lens Finish	Frosted
Lens Material	Plastic
Lensed	Yes
Operating Position	Universal
Power Factor	>0.5
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	150W/100W/50W

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K/4000K/5000K
Dimmable	Non-Dimmable
Hours Rated	15000
Beam Angle (degree)	180
Color Temp	Warm White to Natural Light
CRI	80+
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	2150L/1600L/625L
Volts	120v
Watts	20W/14W/6.5W

PHYSICAL

Lamp Base	Medium Double Contact
Finish	Frost
Housing Color	White
ANSI Base	E26d
Lamp Type	A21
MOD Lamps	2.76
MOL	5.39

ADDITIONAL INFO

Warranty	2-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes
--------------	-----

PACKAGING

UPC	045923144011
Case Cube	0.8689
Case Height	12.61
Case Length	12.6
Case Quantity	24
Case UPC	10045923144018
Case Weight	5.5
Case Width	9.45
EA Cube	0.0247
EA Height	5.44
EA Length	2.8
EA Quantity	1
EA Weight	0.17
EA Width	2.8
Inner Cube	0.1751
Inner Height	5.83
Inner Length	8.78
Inner Quantity	6
Inner UPC	20045923144015
Inner Weight	1.14
Inner Width	5.91
Pack Type	Color Box
Web Length	5.39
Web Width	2.76

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Non-Compliant
Title 20	No
T24/JA8 Compliant	No
US State Ban	CA