

**Watertight Devices, Twist-Lock® Connector, 20A, 3 Phase 250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L15-20R, Yellow**



By Hubbell Wiring Device-Kellems  
Catalog # [HBL27W75](#)

CONN, W/TIGHT, 3P 20A 250V, L15-20R, YL

**Features**

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

**Performance**

Electrical - Current Interrupting - Rated for current interruption per UL498, Electrical - Dielectric Voltage - 2500V AC, Electrical - Max Working Voltage - As marked, Electrical - Temperature Rise - 30°C max per UL498 at rated current, Environmental - UV resistance - All exposed materials are UV stabilized, Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P, Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous, Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)

**Specifications**

Standards - RoHS Compliance Status	CM
EU RoHS Indicator	Contact Manufacturer
Nema Rating	L15-20R
Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards

**Conductor**

Number Of Wires	4-Wire
Wire Size	<ul style="list-style-type: none"> <li>• Min. Cord: 16/3 SJ, 18/3 S, 18/4 SJ, 18/4 S, 18/5 S</li> </ul>

Number Of Poles	<ul style="list-style-type: none"> <li>• Max. Cord: 10/3 S, 10/4 S, 10/5 S</li> </ul> 3-Pole
-----------------	--

**Current**

Amperage Rating	20 A
Voltage Rating Description	3 Phase 250 VAC
Voltage Rating	3 Phase 250 VAC
Current / Amperage Rating	20 A

**Dimensions**

Length	2.51 in
Height	5.69 in
Width	2.51 in
Dimensions	2.51 in x 2.51 in x 5.69 in

**General**

Color	Yellow
UPC	783585131801
Type	Connector Body
Item Type	20A Watertight Twist-Lock® Connector

**Logistics**

Pallet Quantity	550
Carton Quantity	10

**Product Assets**

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)