

HIGHCLERE

MDS2405-AGB/FBL

FINISHES

AGED BRASS w/ SOFT FRENCH BLUE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 14.5"

Width/Diameter: 17.75"

Minimum Height: 17.75"

Maximum Height: 69.5"

Canopy/Backplate: 5.25"

Hanging Type: 54" Chain

Product Weight: 17.16lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 17"

Shade 1 Height: 2"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 21" x 21" x 17"

Carton 1 Weight: 21lb

Shipping Method: Ground

Country of Origin: VN

