Amulet | E24031-24BKNAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Circular bands, like ornaments, descend from thin low voltage cables in a variety of configurations. An evenly diffused LED tube spans the distance of the circular wavy glass shades creating a dazzling lighting effect. A contrasting two-tone Black and Natural Aged Brass finish supports this ornament as seen on the large LED wall sconce.



MEASUREMENTS

DIMENSION	: 8" L x 8.5" W x 21.75" H
MAX OAH	: 143" OAH
CANOPY	: 4.75" W x 1.75" H x 4.75" L
HANGING WEIGHT	: 2.7 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (480 Del.)
BULB	: 1 x 9W LED DC Integrated , 9W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Natural Aged Brass (BKNAB)

GLASS

Clear 24

MATERIAL

Glass, Aluminum, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com