MEESE

90PSL SHELF-TRUX® with Split Lid and Door option
PRODUCT INFO SHEET



The 90PSL combines the double protection of a solid top and durable, lockable doors in a round-trip design for both clean linen delivery and for soiled linen pick up and return.



Ventilated, plastic, repositionable shelves may be slid into vertical position for use as a bulk bin.



Sporting smooth, sleek looks and protective security features, the 90PSL is often specified for luxury properties.

Overview: The 90PSL is a smooth, sleek, versatile, lockable, round-tripper shelf truck, perfect for both clean linen delivery and soiled linen pick up and return. It is a favorite in hospitals, healthcare clinics and luxury properties around the world.

Benefits: The 90PSL comes with two removable and repositionable ventilated polyethylene shelves, a split hinged lid for ergonomic access and lockable doors to deter theft and protect from the elements. When full, this cart is perfect for delivering folded goods, cleanly and efficiently. When empty, these shelves can be converted to the soiled position to form a "wall", making the transportation of soiled linens cleaner and easier. It is made of the stronger and lighter High Density Polyethylene (HDPE) compared to Linear Low Density Polyethylene (LLDPE), common with many competitors. And the 90PSL, like all Meese carts, has a metal free bottom to avoid snags and tears.

Standard Features
- Rotationally molded from waterproof, chemical-resistant High Density Polyethylene (HDPE)
- Torque-resistant, molded-in inserts
- Split hinged top
- Two, non-removable, ventilated, plastic shelves in colonial white
- Two doors that swing 270 degrees flush against cart side
- Recessed handles
- Molded-in door reinforcing bars
- Built-in security lock
- Rotationally molded, smooth poly base
- Four 6" x 2,"gray rubber non-marking Colson casters
- Drain holes

Featured Options (May affect shipping weight)
- Stencil, Mold-in or Mold-on text, logos or graphics
- Nylon cart covers
- Four 8" x 2,"gray rubber non-marking premium casters

Dimensions 50" L x 30¾" W x 64½" O.A.H. Inside Depth: 54"
Capacity 32 Bushels/38 cubic feet
Load Capacity 800 lbs.
Shipping Weight 243 lbs. for standard part only
NOTE: Non-nesting containers; (3) trux side-by-side, 36 per standard trailer

Color Selections

Red #186C	Forest Green #3308C	Royal Blue #2727C	Brilliant Orange #171C	Metallic Silver/ Cool Gray 6	Cadet Blue #303C	Black	Jade Green #16-5942 TPX

1745 Cragmont Street ■ Madison, Indiana 47250-2874 ■ 800-829-4535 ■ Fax: 812-273-1878 ■ meese-inc.com ■ e-mail: customerservice@meese-inc