

GARVEY

B4927-TBZ/PBR

The Garvey sconce reimagines a traditional box lantern with a modern, artistic twist. A rod pierces vertically through the design, suspending a central bead that houses the LED light source. Behind it, a reflective panel amplifies the glow while adding a contemporary dimension. The interplay of the contrasting Textured Bronze and Patina Brass finishes creates visual depth. Available in three sizes, Garvey suits a range of outdoor settings.

FINISHES

TEXTURED BRONZE w/ PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 27"

Width/Diameter: 8"

Canopy/Backplate: 7.25"

Product Weight: 11lb

Extension: 8.5"

Top to Center: 13.5"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear

Shade 1 Top Width: 4.5"

Shade 1 Height: 23.5"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 9

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 50

Title 24: No

Field Serviceable: Yes



SHIPPING

Carton 1: 68" x 27" x 30"

Carton 1 Weight: 15lb

Shipping Method: Truck Only

Country of Origin: VN