
Schaefer® 24CFO-SWDS 24" Washdown-Duty Circulation Fan—5670 CFM, 1/4 HP, 115/230 Volt



- HEAVY-DUTY—ideal for food and beverage processing facilities; kitchens; hospitals; and other clean, corrosive, or humid environments.
- LEGENDARY—greater air movement and superior cooling
- BEST-IN-CLASS—electro-polished blade surface for easy cleaning and minimal bacteria growth
- Matched heavy-duty stainless-steel motor and blades
- 2-year limited warranty

Product Description

The Schaefer® 24CFO-SWDS 24" Washdown-Duty Circulation Fan—5670 CFM, 1/4 HP, 115/230 Volt is the ideal cooling solution for food and beverage processing facilities; kitchens; hospitals; and other clean, corrosive, or humid environments. Engineered to produce greater air movement and superior cooling, it's the right choice no matter the application. The best-in-class design meets USDA and NSF/ANSI/3-A standards, so you know you're getting the highest quality product. The matched heavy-duty stainless-steel motor and blades provide maximum velocity, and the specifically designed, electro-polished blade surface makes this legendary fan easy to clean while supporting minimal bacterial growth. Plus, the fan blades are rigid enough to be washed even while operating. Includes a 2-year limited warranty.



©2021 Pinnacle Climate Technologies, Inc.

Features and Benefits

- Ideal for food and beverage processing facilities; kitchens; hospitals; and other clean, corrosive, or humid environments.
- Engineered to produce greater air movement and superior cooling
- Meets USDA and NSF/ANSI/3-A standards
- Specifically designed, electro-polished blade surface for easy cleaning and minimal bacteria growth
- Maximum velocity for up to 5670 CFM
- Matched heavy-duty stainless-steel motor and blades
- Rigid, trusted blades—washable even while operating
- Corrosion-resistant, OSHA-compliant guards
- Pedestal and stainless-steel wall mounting options available
- Assembled in the USA
- 2-year limited warranty

Key Specs

Model Number	24CFO-SWDS	**Variable Speed**	No
Brand	Schaefer®	**Speed (RPM)**	1725
Warranty	2-year limited warranty	**Thrust (lbf)**	5.32
Net Weight (lb.)	42	**Volts**	115 / 230
Air Flow (CFM)	5670	**Amps**	1.3 / 2.6
Motor Size (HP)	3/4	**Tested**	*S*
Fan Diameter (in.)	24		

©2021 Pinnacle Climate Technologies, Inc.