

# GLINT

F5416-PBR

Inspired by classic RLM silhouettes, Glint reimagines industrial design with character and vintage-inspired details. The ribbed Holophane glass shade adds texture while softly diffusing light. Three suspension arms work to create a clean, structural frame that emphasizes balance and craftsmanship. A Patina Brass finish enhances Glint's retro aesthetic.

## FINISHES

### PATINA BRASS

Coastal Suitable Finish (EPM): No

## DIMENSIONS

Height: 11.5"

Width/Diameter: 16.75"

Minimum Height: 15"

Maximum Height: 85"

Canopy/Backplate: 4.75"

Hanging Type: 72" Chain

Product Weight: 10lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

## Shade

Shade 1: Glass

Shade 1 Finish: Clear Holophane

Shade 1 Top Width: 15"

Shade 1 Height: 7.5"

## ELECTRICAL



### Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: G40

Max Wattage: 25

Bulb Quantity: 1

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND  
WIRE

Gem Box Required (2"x3"):

Dark Sky: No

## SHIPPING

Carton 1: 19" x 19" x 13"

Carton 1 Weight: 13lb

Shipping Method: Ground

Country of Origin: VN

