



Technical Data

Color	Gray
Sizes Available	OS
Packaging	Bagged Pair
Packed	200/Case
Case Dimensions (in)	21.81 x 15.28 x 23.46
Case Weight (lbs)	33.44
Country of Origin	Taiwan
Lens	I/O Mirror
Frame Style	Foam-Lined
Lens Color	Mirror
Lens Coating	Anti-Fog
Temple	Removable
Certifications	ANSI Z87.1, TAA Compliant

UVEX® Tirade™

Rimless Safety Glasses with Foam Padding, I/O Lens and Anti-Fog Coating

- Indirect ventilation channels on the foam and sub-frame provide superior dust filtration keeping debris out of the eyes
- Frameless, unilens design allows for wide-field peripheral vision
- Quick-release hinge system converts easily from temples to headband
- Removable temples and standard adjustable headband included
- Hypoallergenic latex-free option available
- 100% Non-conductive dielectric DesignCan be worn in environments where accidental exposure to electrical charge is possible
- Uvextra® anti-fog coated lens reduces fogging, keeping lenses clear
- Meets ANSI Z87.1+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
S4044	Gray	I/O Mirror	Mirror	AF	603390130328	30603390130329	70603390130327
S4044-EH	Gray				198987170639	10198987170636	20198987170633
S4044-MS					S4044-MS		

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated