




## TEGERA® INFINITY 8803

Learn more

### KNUCKLE DIPPED, DOUBLE COATED PALM

Precision work glove with a unique feeling and ultimate dexterity for jobs in greasy and oily environments. Ultra-light thanks to 18 gg knitting. Knuckle dipped with microfoam coated palm for better grip performance. Withstands contact heat up to 100°C/212°F. Anatomically designed, passes Derma-tests and has Oeko-Tex certificate.

#### CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Durable
- Good grip
- Extra comfortable

#### FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- Oil and grease resistant
- Thin



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping, Contact with moisture, Contact with oil and fat

## PRIMARY ENVIRONMENTS OF USE

Moist environments, Oily and greasy environments, Dirty environments

## PRIMARY AREAS OF USE

Fine assembly, Assembly, Machine operating, Building and construction, Carpentry, Installation work, HVAC installation, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Repair work, Service work, Shop work

## PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Public safety, security and defence, Retail and wholesale, Transport equipment manufacturing, Transportation and logistics, Warehousing

## TYPE OF WORK

Light weight

## SPECIFICATION

**TYPE** Heat protection gloves, Precision work gloves
**CATEGORY** Cat. II
**COLLECTION** Infinity
**KNITTING GAUGE (GG)** 18
**LINING MATERIAL** Nylon
**LENGTH** 225-275 mm
**DEXTERITY** 5
**GRIP DESIGN** Foam grip pattern
**COLOUR** Black
**PAIRS PER: BUNDLE/CARTON** 6/120
**DISPLAY TYPE** Bulk pack
**DIPPING** 3/4 dipped
**DIPPING MATERIAL** Nitrile, Nitrile foam, Waterbased PU
**CUFF STYLE** Knitwrist cuff
**CUFF MATERIAL** Textile
**INNER MATERIAL SPECIFICATION** Nylon, Natural latex
**OUTER MATERIAL SPECIFICATION** Nitrile

## COMPLIANCE

CE Cat. II — TP TC 019:2011

UKCA Cat. II — EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4121X

EN 407:2020 (No flame protection) X1XXXX

ANSI 4 ABR

**Contact heat rating valid for palm area only**

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 6 | XS | 8803-6 | 7340118383989 |
| 7 | S | 8803-7 | 7340118319025 |
| 8 | M | 8803-8 | 7340118319032 |
| 9 | L | 8803-9 | 7340118319049 |
| 10 | XL | 8803-10 | 7340118319001 |
| 11 | XXL | 8803-11 | 7340118319018 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*