Coulee | E30264-125BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Like bridges over a babbling brook, this collection of sconces features a reflective black stainless steel with a wave-like water ripple texture. This decorative detail is fabricated using 304 Grade stainless steel and the sconce's frame is constructed of non-corrosive aluminum. Great for emulating a water feature indoors and suitable for outdoor applications.



MEASUREMENTS

DIMENSION	: 6.25" W x 20.5" H x 2.25" Ext
BACK PLATE	: 6.25" W x 20.5" H x 10" HCO
HANGING WEIGHT	: 6.95 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,240 Rated (1,350 Del.)
BULB	: 4 x 45.5W LED AC Integrated , 46W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)

GLASS

Black Ripple 125

MATERIAL

Stainless Steel, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com