

BRAXTON

F4118-PBR

Braxton speaks to refined utility in both form and function. The shallow RLM-style shade in Patina Brass nods to industrial influence, while the clear optic glass diffuses light beautifully through prismatic ridges. Available as a 1-light flush mount or pendant, Braxton is a versatile fixture for any contemporary space.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 6.5"

Width/Diameter: 18"

Minimum Height: 13.25"

Maximum Height: 56"

Canopy/Backplate: 4.75"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Holophane

Shade 1 Top Width: 8.5"

Shade 1 Bottom L/W: 0" / 8.5"

Shade 1 Height: 4.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 55" x 55" x 27"

Carton 1 Weight: 13lb

Shipping Method: Truck Only

Country of Origin: VN

