

PX43 MET





PX43 MET

Optical system	Color Corrected Infinity Optical System (CCIS®)
Observation tube	360° swivel range, height difference 40mm
Interpupillary distance	48-75mm
Eyepieces	UC-WF 10X/FN22
Diopter adjustment	5
Trinocular light split	20:80
Nosepiece	Quintuple Revolving Nosepiece
Objectives	Plan S-Apo BD 5X ; Plan S-Apo BD 10X ; Plan S-Apo BD 20X ; LPlan S-Apo BD 50X
Stage Size (mm)	Size : 320(W) X 194(L) mm, Stroke : 50 X 50mm
Focus	Course/Fine Focus Knob, Course 42mm/ revolution, Fine 0.2mm/ revolution, 0.002mm/ marks
Transmitted Light	Reflected Light 100W Light House RL100.00
Electronics	115 / 230V~, 60 / 50Hz Halogen Light : 12V / 100W
DIC	Optional
Analyzer	Optional
Polarizer	Optional