Project / Job Name:

Location:

Fixture Type:

Notes:



67-140 - Remote Emergency Light; Weatherproof Low Power Single Head; 3-12V 0.75W; White Finish

WET LOCATION | c UL us LISTED | RoHS COMPLIANT | IP 65

GENERAL

Company	SATCO
EA Height	6.5
EA Width	4.72
EA Length	4.72
Bulb Included	Integrated
Diameter	4.5
Material	Thermo Plastic
Fixture Type	Emergency Light
Status	Active
Style	Utility
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.250-0.063A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5700K
Dimmable	Non-Dimmable
CRI	80+
Operating Temp	-13F to +122F (-25C to +50C)
Lumens	75L
Volts	3V-12V
Watts	0.75W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Universal

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923676017
Case Cube	1.2216
Case Height	10.24
Case Length	14.96
Case Quantity	12
Case UPC	10045923676014
Case Weight	9.92
Case Width	13.78
EA Cube	0.0838
EA Height	6.5
EA Length	4.72
EA Quantity	1
EA Weight	0.66
EA Width	4.72
Pack Type	Box
Web Width	4.5

COMPLIANCE

CA Prop 65	Lead
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified, cULus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026