



PIP® Kilimanjaro™

Type II Full Brim Safety Helmet with HDPE Shell, 4-Point Textile Suspension, Wheel Ratchet Adjustment Vented, With 4-Point Chinstrap

- Lightweight HDPE shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- EPS foam liner provides front, rear and lateral protection from impact and penetration
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Technical Data

Color	Hi-Vis Yellow, Red, Sky Blue, Navy, Hi-Vis Orange, Royal, White, Orange, Dark Green, Gray, Yellow, Black
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	26.00 x 15.50 x 28.50
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Chin Strap	4-Point Polyester
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP642RV-CH-11	Black	OS	848309043591	10848309043598	20848309043595
280-HP642RV-CH-04	Dark Green	OS	848309043713	10848309043710	20848309043717
280-HP642RV-CH-09	Gray	OS	848309043751	10848309043758	20848309043755
280-HP642RV-CH-31	Hi-Vis Orange	OS	848309045793	10848309045790	20848309045797
280-HP642RV-CH-44	Hi-Vis Yellow	OS	848309045830	10848309045837	20848309045834
280-HP642RV-CH-08	Navy	OS	848309045878	10848309045875	20848309045872
280-HP642RV-CH-03	Orange	OS	848309045915	10848309045912	20848309045919
280-HP642RV-CH-15	Red	OS	848309045991	10848309045998	20848309045995
280-HP642RV-CH-17	Royal	OS	848309045953	10848309045950	20848309045957
280-HP642RV-CH-07	Sky Blue	OS	848309046035	10848309046032	20848309046039
280-HP642RV-CH-01	White	OS	616314961779	10616314961776	20616314961773
280-HP642RV-CH-02	Yellow	OS	616314961854	10616314961851	20616314961858