

HIGHCLERE

MDS2402-AGB/FBL

FINISHES

AGED BRASS w/ SOFT FRENCH BLUE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 9.75"

Width/Diameter: 12.75"

Canopy/Backplate: 6"

Product Weight: 7.7lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 12"

Shade 1 Height: 1.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No



SHIPPING

Carton 1: 16" x 16" x 13"

Carton 1 Weight: 10lb

Shipping Method: Ground

Country of Origin: VN