

**Filament lamp, 230V, 6W**

Part no. SL7-L230
Catalog No. 171293
Alternate Catalog No. SL7-L230
EL-Nummer (Norway) 4137641

Delivery program

Product range			Accessories
Basic function accessories			Filament bulbs
Mounting			Ba15d
lifespan		h	3000
Power			6.5 W
Rated operational voltage	U _e	V	230 V
For use with			SL7-L-...
Connection to SmartWire-DT			no

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-30
Operating ambient temperature max.		°C	60

Technical data ETIM 7.0

Lamps (EG000028) / Indication- and signalling lamp (EC000399)			
Electric engineering, automation, process control engineering / Lighting installation, device / Light medium / Indication- and signal lamp (ec1@ss10.0.1-27-11-06-31 [AKE242014])			
Lamp power		W	6.5 - 6.5
Lamp voltage		V	230 - 230
Luminous flux		lm	0
Socket			BA15d
Technology			Incandescent lamp
Lamp shape			Other
Halogen			No
Krypton			No
Xenon			No
Colour			None
Colour temperature		K	2800
Diameter		mm	0
Total length		mm	0
Suitable for torches			No
Suitable for pointer			Yes
Suitable for round flashing luminaire			Yes
Nominal current		mA	0
Average nominal lifespan		h	3000
Energy efficiency class			

