

QUILL

F4740-GLI

Equally captivating with or without the white linen shades, Quill blooms with botanical inspiration. Using dynamic shaping, it creates eye-catching statement pieces with curved armatures and leaf-like bobèche details. A Gilded Ivory finish lends a delicacy to the design. Available as a 1-light sconce and 6- and 8-light chandelier.

FINISHES

Gilded Ivory

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20.25"

Width/Diameter: 40"

Minimum Height: 24.25"

Maximum Height: 94.5"

Canopy/Backplate: 6.5"

Hanging Type: 72" Chain

Product Weight: 15.4lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: White Linen

Shade 1 Top Width: 3"

Shade 1 Bottom L/W: 0" / 6.5"

Shade 1 Height: 7.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 6

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 41" x 37" x 27"

Carton 1 Weight: 36lb

Shipping Method: Truck Only

Country of Origin: PH

