




PINOUT:

P1	COLOR	LABEL	P1	COLOR	LABEL	P1	COLOR	LABEL
1	BLACK	P1	14	BLACK/WHITE	P14	27	RED/BLACK	P27
2	BROWN	P2	15	BROWN/WHITE	P15	28	ORANGE/BLACK	P28
3	RED	P3	16	RED/WHITE	P16	29	YELLOW/BLACK	P29
4	ORANGE	P4	17	ORANGE/WHITE	P17	30	GREEN/BLACK	P30
5	YELLOW	P5	18	YELLOW/WHITE	P18	31	BLUE/BLACK	P31
6	GREEN	P6	19	GREEN/WHITE	P19	32	PURPLE/BLACK	P32
7	BLUE	P7	20	BLUE/WHITE	P20	33	GRAY/BLACK	P33
8	PURPLE	P8	21	PURPLE/WHITE	P21	34	WHITE/BLACK	P34
9	GRAY	P9	22	GRAY/WHITE	P22	35	PINK/BLACK	P35
10	WHITE	P10	23	PINK/WHITE	P23	36	LIGHT GREEN/BLACK	P36
11	PINK	P11	24	LIGHT GREEN/WHITE	P24	37	LIGHT BLUE/BLACK	P37
12	LIGHT GREEN	P12	25	LIGHT BLUE/WHITE	P25	Shell		
13	LIGHT BLUE	P13	26	BROWN/BLACK	P26			

CUSTOMER P/N:	COLOR	LENGTH(xx)
DBC-37FW-05	BLACK	1525+30/-10mm
DBC-37FW-10	BLACK	3050+30/-10mm
DBC-37FW-25	BLACK	7625+80/-10mm

SPEC:

- UL 2464 28AWG*37C+DRAIN+AL JACKET BLACK
IN COLOR OD:9.0mm
- DB 37P FEMALE TYPE BLACK COLOR SHELL NICKEL PLATED
- MOLDING PVC(UL94-V0) BLACK IN COLOR
- MOLDING SCREW 4-40UNC 4*45mm
- HEAT SHRINK TUBE LABEL WHITE IN COLOR L=15MM

Model Name:
D-Sub DB37 Female RS-232
Serial Cable to Lead Wires

Part No.
DBC-37FW-XX

CompuCableUSA