
Torch | E11004-24PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Machined Aluminum tubes of Black, Polished Chrome, or Brass suspend within clear glass overlays. An LED GU10 bulb is recessed within the metal tube providing great directional lighting. Available as a single pendant or as a 4-Light linear pendant.



*max overall height

MEASUREMENTS

DIMENSION	: 28" L x 6" W x 14.75" H
MAX OAH	: 136" OAH
CANOPY	: 6" W x 1" H x 28" L
HANGING WEIGHT	: 9.5 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,200 Rated (1,280 Del.)
BULB	: 4 x 7W LED GU10 , 7W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Triac
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)
Polished Chrome (PC)
Satin Brass (SBR)

GLASS

Clear 24

MATERIAL

Steel + Aluminum + Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 2
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com