



Ironcat®

Premium Top Grain Goatskin Leather MIG Welder's Glove with Split Cowhide Back and Fleece Lining

- Top Grain Goatskin leather construction is the softest, most abrasion-resistant leather and is highly recommended for applications requiring tactile sensitivity
- Top Grain leather is smooth, provides durability and dexterity
- Split cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Gunn cut pattern delivers excellent durability, wear and comfort, especially for heavier gloves
- Fleece lined for additional heat protection
- Stitched with Kevlar® adding strength and burn resistance
- Reinforced thumb crotch strap for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Straight thumb increases comfort in closed-fisted work
- Reinforced pulse protector
- Brown split cowhide gauntlet cuff for added forearm protection and allows for easy on and off



Technical Data

Color	Brown
Sizes Available	M-2XL
Packaging	Pair Tagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	19.02 x 15.00 x 19.02
Case Weight (lbs)	43.48
Country of Origin	Pakistan
Hide	Top Grain Goatskin
Lining	Fleece Pile
Grade	Premium
Cuff	Gauntlet
Palm	Leather
Back	Leather
Closure	Slip On
Thumb	Straight
Stitching	Kevlar
Construction	Cut-and-Sewn, Gunn Cut

Performance Data

ARC Rating	cal/cm2
ARC Rating	cal/cm2

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
6143/M	Brown	M	848309039396	10848309039393	20848309039390
6143/L	Brown	L	848309039358	10848309039355	20848309039352
6143/XL	Brown	XL	848309039433	10848309039430	20848309039437
6143/2XL	Brown	2XL	616314848445	10616314848442	20616314848449