

With touchscreen functionality and PU palm-dipping for high fingertip sensitivity.

TEGERA® 877

Learn more

A SUPER THIN AND FLEXIBLE ESD GLOVE

A super thin and flexible ESD glove with touchscreen functionality and PU palm-dipping for high fingertip sensivity. For ESD-protected work areas where maximum dexterity is needed. The touchscreen functionality ensures seamless transition between duties without having to remove the glove. Thin 18 gg fibre and highly breathable to ensure all-day comfort.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

FUNCTIONS

- For touchscreen
- ESD
- Antistatic/ATEX
- Conforms with IEC 61340-5-1 (ESD)
- Ultra thin
- Super soft

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Contact with dirt, Drying out

PRIMARY ENVIRONMENTS OF USE

Dry environments, Dirty environments

PRIMARY AREAS OF USE

Electronics work, Fine assembly

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Electrical equipment manufacturing, Electricity and gas supply, Electronics manufacturing, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE ESD gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Carbon, Nylon
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Blue
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Rolled edges
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon, Carbon thread
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 3120X

EN 1149-2:1997

IEC 61340-5-1:2016 R < 1.0 x 10^9 Ω

EN 16350:2014 R < 1,0 x 10^8 Ω

ANSI 3 ABR

Do not wash

FEATURES

For touchscreen

SIZE		ARTICLE NUMBER	EAN
5	XXS	877-5	7340118397788
6	XS	877-6	7340118397870
7	S	877-7	7340118397962
8	M	877-8	7340118398051
9	L	877-9	7340118398143
10	XL	877-10	7340118398235
11	XXL	877-11	7340118398327
12	3XL	877-12	7340118398419

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.