
11 In. 13.7W (75W Replacement) Selectable White Round Black LED Flat Panel Ceiling Light With (2-Pack)

Features

- Dependable, long-lasting, energy-efficient replacement for recessed ceiling lighting
- Preset color temperature or adjust after install. Get 3000K/3500K/4000K/5000K/6500K with a flip of a switch
- Ultra-modern slim edge-lit design looks great in any space, including rooms with low ceilings
- **Ideal usage:** Flush Mount Ceiling
- **Special Features:** Color Selectable



Specifications

Item Number	Item Length (In)	Item Width (In)	Item Height (In)
FP11EX6WYBK2	11	11	1.4
Bulb Finish	**Fixture Lens Material**	**Fixture Mount**	**Lens Finish**
Matte Black	Pmma	Ceiling	Frost
Technology	**Brightness (LUMENS)**	**Lumen Efficiency (LPW)**	**Beam Angle**
LED - SMD	1100	80.29	110
Color Accuracy (CRI)	**Color Temperature (CCT)**	**Life Hours**	**Life Years**
80	3000|3500|4000|5000|6500	50000	45.7
Voltage (V)	**Replacement (Wattage)**	**Annual Energy Cost ($)**	**Energy Used (Wattage)**
120	75	1.65	13.7
Battery Operated	**Pack Quantity**	**Bulbs Included**	**Smart**
No	2	Yes	No
Portable	**Dimmable**	**Hardwire**	**Enclosed Fixture Rated**
No	Yes	Yes	No
Safety Location	**CEC Compliant**	**Warranty Years**	
Damp	Not Regulated	5	