



Technical Data

Color	Brown
Sizes Available	M-XL
Packaging	Case
Packed	45 Pair/Case
Case Weight (lbs)	0.00
Country of Origin	United States
Liner Material	PBI
Lining	Nylon Wool
Cuff	Straight
Hem	Hemmed
Construction	Cut-and-Sewn, ESD Safe, Supported
Certifications	TAA Compliant
Product Circularity	Reusable / Launderable

Performance Data

Temperature Resistant	Extreme Heat
Static Control Property	Static Dissipative

QRP® Qualatherm®

Heat & Cold Resistant Electrostatic Dissipative (ESD) Glove with PBI® Outer Shell and Nylon / Wool Lining - 14"

- Dry contact temperatures for -210F to 1400F (-134C to 760C) with no charring, ash or residue
- Ambidextrous pattern permits glove to be worn on either hand, extending wear and reducing costs
- No PCB, asbestos or fiberglass
- ESD protection Static Dissipative 10(9)
- ESD safe compliance to ANSI/ESD S20.20-2014
- RoHS compliant

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-17

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
50GM	Brown	M	616314278624	10616314278621	20616314278628
50GL	Brown	L	616314278617	10616314278614	20616314278611
50GXL	Brown	XL	616314278631	10616314278638	20616314278635