



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

S14208 - 8 Watt ST19 LED; 2000K CCT; Medium Base; Clear Glass; Amber Coil Filament; Dimmable; 120 Volt



GENERAL

| | |
|---------------------------|--|
| Company | SATCO |
| EA Height | 5.89 |
| EA Width | 2.5 |
| EA Length | 2.5 |
| Dimmable Text | Forward or Reverse Phase; Line Voltage |
| Lamp Filament | Spiral |
| Material | Glass |
| Fixture Type | Miniature |
| Status | Active |
| Surge Protection | Built-in surge protection - 2.5KV |
| Total Harmonic Distortion | <10% |
| CCT Selectable | No |
| Wattage Selectable | No |
| Finish Family | Clear |
| Amps | 0.090A |
| Lens Material | Glass |
| Operating Position | Universal |
| Power Factor | >0.7 |
| SDS Class | LED_Lamp |
| Indoor Outdoor | Indoor and Outdoor |
| Product Technology | LED |
| Incandescent Equivalent | 60W |

ELECTRICAL

| | |
|---------------------|-----------------------------|
| CCT (Kelvin Temp) | 2000K |
| Dimmable | Yes-Dimmable |
| Hours Rated | 15000 |
| Beam Angle (degree) | 300 |
| Color Temp | Warm White |
| CRI | 90+ |
| Dimming Type | Linear Dimming, Phase cut |
| Operating Frequency | 60Hz |
| Operating Temp | -25C (-13F) to +40C (+104F) |
| Lumens | 800L |
| Volts | 120v |
| Watts | 8W |

PHYSICAL

| | |
|-----------|-------------|
| Lamp Base | Medium |
| Finish | Clear Amber |
| ANSI Base | E26 |
| Lamp Type | ST19 |
| MOD Lamps | 2.29 |
| MOL | 5.32 |

ADDITIONAL INFO

| | |
|----------------------------|---------|
| Warranty | 2-Years |
| Rated For Enclosed Fixture | Yes |

PACKAGING

| | |
|----------------|----------------|
| UPC | 045923142086 |
| Case Cube | 0.7256 |
| Case Height | 6.82 |
| Case Length | 16.43 |
| Case Quantity | 24 |
| Case UPC | 10045923142083 |
| Case Weight | 4.47 |
| Case Width | 11.19 |
| EA Cube | 0.0213 |
| EA Height | 5.89 |
| EA Length | 2.5 |
| EA Quantity | 1 |
| EA Weight | 0.13 |
| EA Width | 2.5 |
| Inner Cube | 0.1597 |
| Inner Height | 6.5 |
| Inner Length | 7.92 |
| Inner Quantity | 6 |
| Inner UPC | 20045923142080 |
| Inner Weight | 0.97 |
| Inner Width | 5.36 |
| Pack Type | Color Box |
| Web Length | 5.32 |
| Web Width | 2.29 |

COMPLIANCE

| | |
|-----------------|-----------------|
| CA Prop 65 | Lead |
| Dark Sky Rated | No |
| FCC Compliant | Yes |
| Location Rating | Wet |
| NSF Approved | No |
| ROHS Compliant | Yes |
| Safety Listing | cULus |
| California Ban | Lawful for sale |
| Title 20 | Exempt |
| T24 Compliant | No |