







PRODUCT DESCRIPTION

Horizontal Spans of natural wood frame an evenly diffused LED omnidirectional light source. Choose from genuine Walnut with Black or Natural Aged Brass accents or solid oak in a hand-applied Driftwood finish. Whether surface mounted or suspended as a pendant, this collection provides a natural touch to an otherwise modern, minimalist design.



MEASUREMENTS

DIMENSION	: 45.25" W x 4.75" H x 4.75" Ext
CANOPY	: 11.75" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 5.3 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,400 Rated (1,800 Del.)
BULB	: 1 x 30W LED DC Integrated , 30W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Driftwood / Charcoal (DWCHL)

Walnut / Black (WNBK)

Whit Alabaster / Natural Aged Brass (WANAB)

MATERIAL

Wood, Acrylic, Aluminum, Steel

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com