SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



62-8002 - Holland; LED Wall Sconce; 10 Watt; 2700K/3000K/3500K CCT; Gun Metal/Light Oak Finish

90+ CRI | DIMMABLE | ETL | FC | RoHS | CCT SELECTABLE | 25,000 HOURS | 3 YEAR WARRANTY | 120-277V | IP 20

GENERAL

Company	NUVO
EA Height	8.47
EA Width	10.63
EA Length	26.4
Mounting Height	1.5
Mounting Length	22.5
Mounting Width	4.75
Bulb Included	Integrated
Extends (in)	5.5
Shade Finish	Light Oak
Material	Aluminum / Steel
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<10%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Holland
Finish Family	Gray
Amps	0.250A
Lens Finish	Frosted
Lens Material	Acrylic
Lensed	Yes
Power Factor	>0.9
Shade Material	Wood
Shade Shape	Curved
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	40W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K
Dimmable	Yes-Dimmable
Hours Rated	25000
Beam Angle (degree)	120
Color Temp	Warm White to Neutral White
CRI	90+
Dimming Type	Phase cut
Operating Frequency	50/60Hz
Operating Temp	-40F to +194F (-40C to +90C)
Lumens	1800L
Volts	120V-277V
Watts	10W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Gunmetal Gray
Housing Color	Gunmetal
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Square

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416477
Case Cube	1.3756
Case Height	8.47
Case Length	26.4
Case Quantity	1
Case UPC	10045923416474
Case Weight	9.24
Case Width	10.63
EA Cube	1.3756
EA Height	8.47
EA Length	26.4
EA Quantity	1
EA Weight	9.24
EA Width	10.63
Pack Type	Kraft Box
Web Height	23.5
Web Width	7.75

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026