




PVC Individual bag:

1. Label#: DB26 male to lead wire, 5ft DBC-26HDMW-05 Rev A1
DB26 male to lead wire, 10ft DBC-26HDMW-10 Rev A1
2. Label#: Prop65 label or print
3. Bare End wires require wrapping protection Bundle PVC bag
Per 10 pcs individuals packed together
Label#: DBC-26HDMW-05 10pcs YYWW (date code)
Label#: DBC-26HDMW-10 10pcs YYWW (date code)

SPEC:

1. CABLE: UL2464 28AWG*26C+DRAIN+AL JACKET BLACK IN COLOR OD: 6.5mm.
2. DB 26P MALE TYPE BLACK COLOR SHELL NICKEL PLATED.
3. HEAT SHRINK TUBE LABEL WHITE IN COLOR L=15mm.
4. MOLDING SCREW 4-40UNC 4*38.5mm.
5. MOLDING PVC (UL94-V0) BLACK IN COLOR.
6. DUST CAP.

PINOUT:

P1	COLOR	LABEL	P1	COLOR	LABEL
1	BLACK	P1	14	BROWN/BLACK	P14
2	BROWN	P2	15	RED/BLACK	P15
3	RED	P3	16	ORANGE/BLACK	P16
4	ORANGE	P4	17	YELLOW/BLACK	P17
5	YELLOW	P5	18	GREEN/BLACK	P18
6	GREEN	P6	19	BLUE/BLACK	P19
7	BLUE	P7	20	PURPLE/BLACK	P20
8	PURPLE	P8	21	GRAY/BLACK	P21
9	GRAY	P9	22	WHITE/BLACK	P22
10	WHITE	P10	23	PINK/BLACK	P23
11	PINK	P11	24	LIGHT GREEN/BLACK	P24
12	LIGHT GREEN	P12	25	LIGHT BLUE/BLACK	P25
13	LIGHT BLUE	P13	26	BROWN/WHITE	P26

SHELL DRAIN

REV	DATE	PROJECTION	DRAWN BY	CHECKED BY	SALES	APPROVAL BY	Model Name:	CUSTOMER	Codes	SHEET NO.
A/0	2025-12-22	<i>milan</i>	<i>2025-12-22</i>	<i>2025-12-22</i>		<i>Jim</i>	D-Sub High Density DB26 Male RS-232 Serial Cable to Lead Wires			
			SCALE:	UNIT: mm	DATE: 2025-12-22			P/N:		
								DBC-26HDMW-**		

CompuCable^{USA}