
Alumilux Tilt | E41331-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 3" W x 5.25" H x 2.75" Ext
BACK PLATE	: 2.5" W x 4.5" H x 2.25" HCO
HANGING WEIGHT	: 0.95 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 700 Rated (360 Del.)
BULB	: 1 x 8W LED DC Integrated , 8W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)
White (WT)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com