

Part #	Power			Max Head	Max Flow	Impeller Mat'l	Exterier Mat'l	Weight (lbs)
	HP	Volt	Amp					
MAS0470S15A-230INT MAS0470S15A-230EXT	2	230	11	443 ft	25 gpm	Stainless steel	Stainless steel	45

	MAS0470S15A-230INT	MAS0470S15A-230EXT
D MAX	4	4
NPT	1.25	1.25
C (inch)	17.32	19.17
B (inch)	20.04	20.04
A (inch)	37.36	39.21

Features & Technical Specifications:

- 4" deep well submersible pump, 15 stage, 443 feet max head (open tank).
- All stainless steel impellers never break.
- Patented impeller provides high flow: 25GPM (max), 13 GPM (rated).
- Solid stainless steel body with heavy duty cast iron or stainless discharge
- Industrial grade heavy duty, also good for home usage
- MAS0470S15A-230INT is 2 wire pumps with 3 wires (2 wires + ground wire) and have a built in capacitor. Do NOT need an external control box!
- MAS0470S15A-230EXT is 3 wire pumps with 4 wires (3 wires + ground wire), and come with external control box (starter box with a capacitor). Must wire the control box correctly!!
- Thermal protection for longer life and powerful start.
- 1¼" NPT discharge. No check valve for easy winterization.
- Designed to fit inside 5" ID or larger pipe/well casing
- High efficiency, hermetically sealed motor is thermally protected to prevent overheating
- Water temperature: (32 ~113oF). Trans medium's Ph: 6.5~ 8.5

