

YSR4CFX8CFXLTCKITC

Attributes	Values
Application	Wire Reducing Splice
AWG Size	4 AWG - 8 AWG
Barrel Style	Skived
Barrel Type	Standard
Coating	Tin-Plated
Collection Name	HYREDUCER
Color Code	Gray/Red
Cond. Material	Copper
CSA Approved	No
cUL Approved	No
cULus Approved	No
Die Index	8;49
ETL Approved	No
Height (in)	0.27
Length (in)	1.5
Length L2 (in)	0.74
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Power Cond. AWG Size	4 - 8 AWG
Strip Length (in)	0.71
Temperature Rating	194 Deg C
Voltage	35 kV
Width (in)	0.38