

JUN-AIR A UNIT OF IDEX CORPORATION BENTON HARBOR, MI U.S.A.	GAST MANUFACTURING INC. A Unit of IDEX Corporation Post Office Box 97 Benton Harbor, Michigan Ph: 269/926-6171 Fax: 269/925-8288	PART NUMBER: RTD904	REV. G

NOTES:
1. ALL DIMENSIONS ARE FOR REF. USE ONLY.
2. PRODUCT DIMENSIONS: U.S. IMPERIAL (inches).
3. * = TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
4. INSTALLATION: THIS PUMP MUST BE INSTALLED IN AN ENCLOSURE.
5. CLVS: -10% OF NOMINAL VOLTAGE LISTED BELOW.

SOUND LEVEL	50 dB(A) at 1 meter
NORMAL AMBIENT	+10 - +40°C
RELATIVE HUMIDITY	10 - 95% (NON-CONSENSING)
REGULATORY	UL1450 / CE / CSA22.2
CLVS	99V / 198V
MAX. DUTY	120 PSI / 8 BAR


JAN 28 2021








Product Performance

THE PERFORMANCE CURVE IS A NOMINAL APPROXIMATION FOR THE MODEL LESS ACCESSORIES, INTAKE FILTERS/EXHAUST MUFFLERS & ACCUMULATION OF CONTAMINANTS WILL DECREASE THE FLOW OF AIR.









Product Specifications

ITEM NUMBER	ELECTRICAL	SERVICE		HP.	kW.	NET WT.		AMPS	CAPACITOR
		FILTERS	COMPRESSOR			lbs.	kg.		
1770008	115V, 50/60Hz	2000 hrs.	8000 hrs.	1/2	.37	65	29.48	4.8/5.3	30.0/370V
1770009	230V, 50/60Hz	2000 hrs.	8000 hrs.	1/2	.37	65	29.48	2.6/2.9	30.0/370V
1770010	230V, 50/60Hz	2000 hrs.	8000 hrs.	1/2	.37	65	29.48	2.6/2.9	30.0/370V
1770014	230V, 50/60Hz	2000 hrs.	8000 hrs.	1/2	.37	65	29.48	2.6/2.9	30.0/370V
1770018	100V, 50/60Hz	2000 hrs.	8000 hrs.	1/2	.37	65	29.48	5.0/5.8	35.0/370V