Pierce | E24229-122BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An elongated profile with piercing statement, this series of pendants feature thin black wires that support a tapered metal pendant. Recessed in this form is a high powered LED that illuminates a brilliantly faceted crystal element with etched details inside its form to capture light and enhance its beauty. Available in Gold or Matte Black, the design complements both modern and many transitional interiors. A coordinating ADA compliant wall sconce was designed with a rigid stem for public spaces and has been sealed for use in damp locations.



*max overall height

MEASUREMENTS

DIMENSION	: 24.75" L x 24.75" W x 19" H
MAX OAH	: 141" OAH
CANOPY	: 24.75" W x 1.75" H x 24.75" L
HANGING WEIGHT	: 30 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,200 Rated (1,060 Del.)
BULB	: 12 x 3W LED DC Integrated , 36W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Gold (GLD)

GLASS

Clear Crystal 122

MATERIAL

Crystal, Aluminum, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com