Canello | E30094-01BK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 48" L x 4.5" W x 48" H x 4" Ext
BACK PLATE	: 4.5" W x 4.5" H x 24" HCO
HANGING WEIGHT	: 3.5 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,200 Rated (3,140 Del.)
BULB	: 1 x 40W LED DC Integrated , 40W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Any

FINISHES OPTION

Black (BK)

GLASS

White 01

MATERIAL

Aluminum, PC

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com