Penrose | E21262-GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A cubist work of art, the Penrose collection carefully calculates the structural form of a cube space when corners do not meet. This tracery of this shape is emphasized by its dedicated LED light source housed within aluminum channels and then cast in various directions. Available in Matte Black or Gold, this series is a feat of human engineering in design. Translating a mathematical challenge into a sculptural work of art with the function of delivering light to interior spaces.



*max overall height

MEASUREMENTS

DIMENSION	: 16" L x 16" W x 16" H
MAX OAH	: 138" OAH
HANGING WEIGHT	: 8.16 lb

LAMPING

INPUT VOLTAGE	: V
LUMENS	: 2,700 Rated (1,700 Del.)
BULB	: 1 x 54W LED DC Integrated , 54W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Gold (GLD)

MATERIAL

Aluminum, Steel

RATINGS

Dry Location

ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com