



FFBF284SSIM



67.75" x 27.63" x 26.25" (H x W x D)

Frost-free ENERGY STAR certified bottom freezer refrigerator with icemaker in stainless steel

Highlights:

ENERGY STAR certified to help save on energy bills and maximize efficiency

Factory-installed icemaker ensures a steady supply of ice

True frost-free operation saves you maintenance by preventing icy buildup

Product Features:

Counter Depth Bottom Freezer Refrigerator	13.8 cu.ft. refrigerator-freezer in a unique 27.63" W x 26.25" D fit ideal for smaller kitchens and apartments
ENERGY STAR certified	Recognized as the Most Efficient of ENERGY STAR 2023
CEE Tier I qualified	Efficient design meets CEE Tier I specifications, using 20% less energy than DOE standards require for this product category
Factory-installed icemaker	Freezer section is equipped with a pre-installed icemaker that keeps a steady supply of crescent ice
Stainless steel doors	Stainless steel doors with a horizontal grain and gentle curve offer a professional look for any kitchen
Smudge-resistant coating	Stainless steel features a protective film that helps to reduce smudges and is easy to clean with a gentle wipe
Large capacity	Generous capacity inside a counter deep 27" footprint
Frost-free operation	No-frost operation ensures reduced maintenance
Digital temperature control	Innovative control panel located inside the refrigerator makes it easy to manage the refrigerator and freezer temperature at the touch of a button



FFBF284SSIM Specifications:

Overview	
Nominal Height	68.0" (173 cm)
Height of Cabinet	67.25" (171 cm)
Height to Hinge Cap	67.75" (172 cm)
Nominal Width	28.0" (71 cm)
Width	27.63" (70 cm)
Width with Door Open	28.38" (72 cm)
Nominal Depth	27.0" (69 cm)
Depth	26.25" (67 cm)
Depth with Handle	27.75" (70 cm)
Depth with door at 90°	51.38" (131 cm)
Capacity	13.8 cu.ft. (391 L)
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Platinum
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	420.0kWh/year
Amps	2.0
Voltage/Frequency	115 V AC/60 Hz
Weight	200.0 lbs. (91 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101089973
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Interior Drawers	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	37.0" (94 cm)
Refrigerator - Interior Width	23.5" (60 cm)
Refrigerator - Interior Depth	19.0" (48 cm)
Refrigerator - Capacity	9.97 cu.ft

Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	22.63" (57 cm)
Freezer - Interior Width	22.13" (56 cm)
Freezer - Interior Depth	16.63" (42 cm)
Freezer - Capacity	3.83 cu.ft
Gallon Door Storage	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	2.47 oz.
Level Legs	2
Interior Height - Drawer 1	10.5" (27 cm)
Interior Width - Drawer 1	22.13" (56 cm)
Interior Depth - Drawer 1	16.63" (42 cm)
Compressor Step Height	10.5" (27 cm)
Compressor Step Width	23.5" (60 cm)
Compressor Step Depth	5.13" (13 cm)

