Moonscapes | E24972-BCN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A triumph of scale, craft, and light, Moonscapes transforms celestial inspiration into a breathtaking installation. Monumental in form yet ethereal in presence, each irregularly shaped panel evokes the cratered terrain of the lunar surface with dramatic texture and depth. Precision edge-lit LED technology is seamlessly embedded within a tailored stainless-steel band, guiding soft, diffused light across the cratered surface with astonishing clarity. The result is an illuminated landscape that appears to hover midair--suspended on near-invisible low-voltage cables--achieving both levity and impact. Engineered for large spaces with architectural ambition, Moonscapes fuses technical mastery with poetic design, offering a bold, unforgettable focal point.



MEASUREMENTS

DIMENSION	: 13.5" L x 6" W x 20.5" H
MAX OAH	: 140" OAH
CANOPY	: 6" W x 1.75" H x 6" L
HANGING WEIGHT	: 4.62 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,600 Rated (1,230 Del.)
BULB	: 1 x 20W LED PCB Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Brushed Champagne (BCN)

Polished Chrome (PC)

MATERIAL

Stainless Steel, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com