



Project / Job Name:

Location:

Fixture Type:

Notes:

S29885 - 7 Watt PLT LED; 3K/35K/4K/5K CCT; GX24d Base; Omni; Type B; 120-277 Volt



GENERAL

Company	SATCO
EA Height	5.08
EA Width	2.05
EA Length	2.05
Lamp Ballast Type AB	Type B
Lamp Filament	LED
Material	Plastic / Aluminum
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<25%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Amps	0.060/0.026A
IOT Enabled	No
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Lensed	Yes
Minimum Compartment Size	Length 11.81 in. Width 6.31 in. Height: 2.75 in.
Operating Position	Universal
Power Factor	>0.9
SDS Class	LED_Lamp
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	18W

ELECTRICAL

CCT (Kelvin Temp)	3000K/3500K/4000K/5000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	360
Color Temp	Soft White to Natural Light
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	960L
Volts	120V-277V
Watts	7W

PHYSICAL

Lamp Base	GX24d (2-Pin)
Finish	WHITE
Housing Color	White
ANSI Base	GX24d
Lamp Type	PLT
MOD Lamps	2.0
MOL	4.9

ADDITIONAL INFO

Warranty	5-Years
Rated For Enclosed Fixture	Yes

FEATURES

Flicker Free	No
--------------	----

PACKAGING

UPC	045923298851
Case Cube	0.4344
Case Height	6.0
Case Length	13.6
Case Quantity	24
Case UPC	10045923298858
Case Weight	8.39
Case Width	9.2
EA Cube	0.0124
EA Height	5.08
EA Length	2.05
EA Quantity	1
EA Weight	0.31
EA Width	2.05
Pack Type	Color Box
Web Length	4.9
Web Width	2.0

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus - Certified
Title 20	Exempt
T24/JA8 Compliant	No