Travertine | E11051-01TVGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

The use of this stone has been central to the building blocks of our history. Reimagined in a modern context, columns of Travertine are assembled alongside LED tubes in an attractive, minimalist composition. The perfect neutral for a space that is searching for more organic elements, the LED light source is evenly diffused withing Matte White acrylic with Gold-plated accents. Available as a sconce and in multiple configurations of pendants.



MEASUREMENTS

DIMENSION	: 2.5" L x 2.5" W x 15" H
MAX OAH	: 137" OAH
CANOPY	: 5.5" W x 1.5" H x 5.5" L
HANGING WEIGHT	: 3.3 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,000 Rated (900 Del.)
BULB	: 1 x 20W LED DC Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Travertine / Gold (TVGLD)

GLASS

White 01

MATERIAL

Stone,Steel,Acrylic

RATINGS

cETLus
Dry Location
ADA

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com