

### Overview


#### Overload relays for standard applications

The following optional accessories are available for the 3RU11 thermal overload relays:

- Terminal support for stand-alone installation of overload relay sizes S00 to S3
- Mechanical RESET (for all sizes)

- Cable release for resetting devices which are difficult to access (for all sizes)
- Electrical remote RESET module in three voltage variants (for all sizes)
- Terminal covers

### Selection and ordering data

Version	Size	DT	Article No.	Price per PU	PU (UNIT, SET, M)	PS*	PG
<b>Terminal supports for stand-alone installation</b>							
 <p>3RU19.6-3AA01</p>	For separate mounting of overload relays; screw and snap-on mounting onto TH 35 standard mounting rail; size S3 also for TH 75 standard mounting rail	S00	▶	<b>3RU1916-3AA01</b>	1	1 unit	41F
		S0	▶	<b>3RU1926-3AA01</b>	1	1 unit	41F
		S2	▶	<b>3RU1936-3AA01</b>	1	1 unit	41F
		S3	▶	<b>3RU1946-3AA01</b>	1	1 unit	41F
<b>Mechanical RESET</b>							
 <p>3RU1900-1A with pushbutton and extension plunger</p>	<b>Resetting plungers, holders and formers</b>	S00 ... S3	▶	<b>3RU1900-1A</b>	1	1 unit	41F
	<b>Pushbuttons with extended stroke</b> (12 mm), IP65, ∅ 22 mm	S00 ... S3	B	<b>3SB3000-0EA11</b>	1	1 unit	41J
	<b>Extension plungers</b> For compensation of the distance between the pushbutton and the unlatching button of the relay	S00 ... S3	A	<b>3SX1335</b>	1	1 unit	41J
<b>Cable releases with holder for RESET</b>							
 <p>3RU1900-1.</p>	For ∅ 6.5 mm holes in the control panel; max. control panel thickness 8 mm	S00 ... S3	▶	<b>3RU1900-1B</b>	1	1 unit	41F
	<ul style="list-style-type: none"> <li>• Length 400 mm</li> <li>• Length 600 mm</li> </ul>	S00 ... S3	▶	<b>3RU1900-1C</b>	1	1 unit	41F
<b>Modules for remote RESET, electrical</b>							
 <p>3RU1900-2A.71</p>	Operating range 0.85 ... 1.1 x $U_N$ , Power consumption AC 80 VA, DC 70 W, ON period 0.2 ... 4 s, switching frequency 60/h	S00 ... S3	A	<b>3RU1900-2AB71</b>	1	1 unit	41F
	• 24 ... 30 V AC/DC	S00 ... S3	A	<b>3RU1900-2AF71</b>	1	1 unit	41F
	• 110 ... 127 V AC/DC	S00 ... S3	A	<b>3RU1900-2AM71</b>	1	1 unit	41F
	• 220 ... 250 V AC/DC	S00 ... S3	A				
<b>Terminal covers</b>							
	<b>Covers for cable lugs and busbar connections</b>						
	• Length 55 mm	S3	B	<b>3RT1946-4EA1</b>	1	1 unit	41B
	<b>Covers for box terminals</b>						
	• Length 20.6 mm	S2	B	<b>3RT1936-4EA2</b>	1	1 unit	41B
	• Length 20.8 mm	S3	▶	<b>3RT1946-4EA2</b>	1	1 unit	41B