

CELINE

H1090701-AGB

Inspired by retro silhouettes, Celine calls on mid-century style with a twist. The domed spot-plated opal glass shade glows softly, diffusing light evenly throughout the entire form. Thin gold pinstripes trace the shade, giving shape to the edges. This sophisticated everyday staple is available as a 1-light semi-flush in two sizes and as a pendant.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 14.75"

Width/Diameter: 15"

Minimum Height: 18"

Maximum Height: 70.25"

Canopy/Backplate: 5.5"

Hanging Type: 54" Chain

Product Weight: 9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Opal Glossy with Gold Leaf Trim

Shade 1 Top Width: 15"

Shade 1 Height: 9.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 19" x 19" x 18"

Carton 1 Weight: 13lb

Shipping Method: Ground

Country of Origin: VN

