Alumilux Glow | E41280-BK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 10" W x 10" H x 1.5" Ext
MAX OAH	: 1.5" OAH 7.01" W x 0.83" H
HANGING WEIGHT	: 3.44 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,050 Rated (831 Del.)
BULB	: 2 x 7.5W LED PCB Integrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90+ CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

- Black (BK)
- Satin Aluminum (SA)
- White (WT)

MATERIAL

Aluminum, Acrylic

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com