



Post Office Box 97
Benton Harbor, Michigan
Ph: 616/926-6171
Fax: 616/925-8288

PART NUMBER:
LTD107

REV.
C

Product Specifications

Model Number	MAX. PRESS.		MAX. SPEED	HP	kW	Net Wt.	
	bar.	PSI				lbs.	kg
8AM-FRV-2B	7.0	100	2,500 RPM	5.0	4.0	27	12,2
8AM-FRV-30A	7.0	100	2,500 RPM	5.0	4.0	27	12,2

SOUND LEVEL 105 dba MAX.

NORMAL AMBIENT +1°C. - 120°C.

RELATIVE HUMIDITY 0% - 100%

ENVIRONMENT HAZARDOUS AMBIENT COMBUSTIBLE GAS AND DUST +1°C TO +40°C
CONFORMS TO EUROPEAN STANDARD EN13463-1 NON-ELECTRICAL
EQUIPMENT FOR EXPLOSIVE ATMOSPHERES GROUP II CAT 2 (GAS & DUST)
PROTECTED BY CONSTRUCTION (SURFACE TEMP. RATED 135°C).

* TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.

