



# LED WALL PACK FIXTURE

## Tunable Wattage & CCT



### PRODUCT FEATURES

- **Tunable Power**
- **Tunable CCT - 3000K / 4000K / 5000K**
- Die-Cast Aluminum Alloy Housing
- Bronze Finish
- 120-277 Voltage Rating, PF > 0.9
- CRI > 80
- 135 Lm/W
- 0-10V Dimming
- Integrated Dusk-to-Dawn Photocell
- PC Lens
- Viewing Angle - 90° x 140°
- IP65 Rating - Suitable for Wet Locations
- ETL Certified
- DLC Listed
- 50,000 Hour Lifetime Rating
- 5-Year Limited Warranty
- Operating Temperature Range: -40°F to 113°F (-40°C to 45°C)

### PRODUCT SPECIFICATIONS

MODEL	ITEM #	POWER (W)	LUMENS (LM)	INPUT VOLTAGE (V)	DIMENSIONS (IN) (L x W x H)
CLW12-25W-H-TCP	L25WTUNWMCL12	15W/20W/25W	2,050 - 3,375	120-277	5.79 X 8.07 X 3.09

