


Features and Benefits

Heavy Duty Commercial Standard Hospital Grade GFCI Receptacles

- Fed. Spec UL Listed, Hospital Grade
- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple



Hospital Grade ●

Rating	Color	Standard	Night Light Two LED Night Lights	Alarm	Assembled in USA
	Black	GFRST82BK	GFRST82BKNL	GFRST82BKB	GFRST82BKU
	Brown	GFRST82	GFRST82NL	GFRST82B	GFRST82U
	Gray	GFRST82GY	GFRST82GYNL	GFRST82GYB	GFRST82GYU
	Ivory	GFRST82I	GFRST82INL	GFRST82IB	GFRST82IU
	Light Almond	GFRST82LA	GFRST82LANL	GFRST82LAB	GFRST82LAU
	Red	GFRST82R	GFRST82RNL	GFRST82RB	GFRST82RU
	White	GFRST82W	GFRST82WNL	GFRST82WB	GFRST82WU
	Black	GFRST83BK	GFRST83BKNL	GFRST83BKB	GFRST83BKU
	Brown	GFRST83	GFRST83NL	GFRST83B	GFRST83U
	Gray	GFRST83GY	GFRST83GYNL	GFRST83GYB	GFRST83GYU
	Ivory	GFRST83I	GFRST83INL	GFRST83IB	GFRST83IU
	Light Almond	GFRST83LA	GFRST83LANL	GFRST83LAB	GFRST83LAU
	Red	GFRST83R	GFRST83RNL	GFRST83RB	GFRST83RU
	White	GFRST83W	GFRST83WNL	GFRST83WB	GFRST83WU

Hospital Grade ● SNAPConnect®



Rating	Color	Standard
	Black	GFRST82SNAPBK
	Brown	GFRST82SNAP
	Gray	GFRST82SNAPGY
	Ivory	GFRST82SNAPI
	Light Almond	GFRST82SNAPLA
	Red	GFRST82SNAPR
	White	GFRST82SNAPW
	Black	GFRST83SNAPBK
	Brown	GFRST83SNAP
	Gray	GFRST83SNAPGY
	Ivory	GFRST83SNAPI
	Light Almond	GFRST83SNAPLA
	Red	GFRST83SNAPR
	White	GFRST83SNAPW

SNAPConnect® Right Angle Pigtailed Terminal



Description	Type	Catalog Number
Clear right angle terminal with 6 inch leads, 600V, #12 AWG THHN/THWN-2, Polycarbonate housing material.	Solid Stranded	SNAP1RA SNAP2RA
Same as above. Assembled in USA.	Solid Stranded	SNAP1RNA SNAP2RNA
Clear right angle terminal with 6 inch leads #12 AWG THHN/THWN-2; Polycarbonate housing material with WAGO terminals.	Solid Stranded	SNAP1RAM2 SNAP2RAM2
Same as above. Assembled in USA.	Solid Stranded	SNAP1RNAM2 SNAP2RNAM2

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles are furnished with a matching color thermoplastic wallplate, 20 amp feed-through capability.

Features and Benefits

Commercial Standard Hospital Grade ● GFCI Receptacles

- Fed. Spec UL Listed, Hospital Grade
- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple



GFRST82WNL



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

Hospital Grade ● GFCI Receptacles

Description	Rating	Color	Catalog Number	
Standard, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BK	GFRST83BK
		Brown	GFRST82	GFRST83
		Gray	GFRST82GY	GFRST83GY
		Ivory	GFRST82I	GFRST83I
		Light Almond	GFRST82LA	GFRST83LA
		Red	GFRST82R	GFRST83R
		White	GFRST82W	GFRST83W
Assembled in USA, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BKU	GFRST83BKU
		Brown	GFRST82U	GFRST83U
		Gray	GFRST82GYU	GFRST83GYU
		Ivory	GFRST82IU	GFRST83IU
		Light Almond	GFRST82LAU	GFRST83LAU
		Red	GFRST82RU	GFRST83RU
		White	GFRST82WU	GFRST83WU
Night Light Two LED Night Lights, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BKNL	GFRST83BKNL
		Brown	GFRST82NL	GFRST83NL
		Gray	GFRST82GYNL	GFRST83GYNL
		Ivory	GFRST82INL	GFRST83INL
		Light Almond	GFRST82LANL	GFRST83LANL
		Red	GFRST82RNL	GFRST83RNL
		White	GFRST82WNL	GFRST83WNL
Alarm, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BKB	GFRST83BKB
		Brown	GFRST82B	GFRST83B
		Gray	GFRST82GYB	GFRST83GYB
		Ivory	GFRST82IB	GFRST83IB
		Light Almond	GFRST82LAB	GFRST83LAB
		Red	GFRST82RB	GFRST83RB
		White	GFRST82WB	GFRST83WB
SNAPConnect®, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82SNAPBK	GFRST83SNAPBK
		Brown	GFRST82SNAP	GFRST83SNAP
		Gray	GFRST82SNAPGY	GFRST83SNAPGY
		Ivory	GFRST82SNAPI	GFRST83SNAPI
		Light Almond	GFRST82SNAPLA	GFRST83SNAPLA
		Red	GFRST82SNAPR	GFRST83SNAPR
		White	GFRST82SNAPW	GFRST83SNAPW



GFRST82R



GFRST83INL



GFRST83BKB



GFRST83SNAPGY

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles are furnished with a matching color thermoplastic wallplate, 20 amp feed-through capability. Requires pigtailed connector see page M-14.