



Project / Job Name:

Location:

Fixture Type:

Notes:

S13093 - 50 Foot Temporary String Light; E26; Plastic Cages; Lamps not included



GENERAL

Company	SATCO
EA Height	7.87
EA Width	11.02
EA Length	14.17
Bulb Included	No
Material	Polycarbonate (PC)
Fixture Type	Miniature
Product Notes	The maximum wattage rating of each individual lamp holder shall not exceed 150W with a maximum of 750W per individual string
Status	Active
Style	Utility
Wire Color	Yellow
CCT Selectable	No
Wattage Selectable	No
Finish Family	Yellow
Amps	15.000A
SDS Class	LED Fixture
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Fixture Lamp Count	5

ELECTRICAL

Dimmable	Non-Dimmable
CRI	80+
Operating Temp	-40F to +104F (-40C to +40C)
Volts	120v

PHYSICAL

Lamp Base	Medium
Finish	Yellow / Black
ANSI Base	E26

ADDITIONAL INFO

Warranty	1-Year
----------	--------

FEATURES

Flicker Free	No
--------------	----

PACKAGING

UPC	045923130939
Case Cube	0.7112
Case Height	7.87
Case Length	14.17
Case Quantity	1
Case UPC	10045923130936
Case Weight	5.95
Case Width	11.02
EA Cube	0.7112
EA Height	7.87
EA Length	14.17
EA Quantity	1
EA Weight	5.95
EA Width	11.02
Pack Type	Color Box
Web Height	8.27
Web Length	4.8
Web Width	4.8

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Certified
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No