MASTER®
THE PROFESSIONAL'S CHOICE SINCE 1953

Master MAC-30D - 30" Direct Drive Drum Fan—6450 CFM, 1/3 HP, 120 Volt



- DURABLE—great for garages, barns, or workshops, or outside events
- POWERFUL—steel construction
- INDUSTRY-LEADING—high airflow for up to 6450 CFM
- Machined industrial motor, steel-coated safety grille, built-in handle, and more
- 1-year limited warranty

Product Description

Get ready for an unrivaled cooling solution like no other. The Master 30" High Capacity Direct-Drive Barrel Fan will blow you away with the massive amount of air it moves and its quiet, direct-drive operation. When you need to save on A/C and cool a giant indoor or outdoor space, this fan has you covered. With rock-solid wheels for portability and the durable steel construction you demand, you know you're getting the best. This is a true workhorse air circulator. ***Master – built for power.***



©2026 Pinnacle Climate Technologies

Features and Benefits

- Great for garages, barns, or workshops, or outside events
- Powerful steel construction
- High airflow for up to 6450 CFM
- 1/3 HP industrial motor
- Built-in handle
- Steel-coated safety grille
- 3 variable speed settings
- Rock-solid wheels
- 1-year limited warranty

Key Specs

Model Number	MAC-30D
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	37.5
Air Flow (CFM)	6450 / 5600 / 5100
Motor Size (HP)	1/3
Variable Speed	Yes
Volts	120
Amps	1.8
Dimensions (L x W x H) (in.)	33 x 11.5 x 33

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2026 Pinnacle Climate Technologies